

Fuseholders 6.3 x 32mm (1 1/4" x 1/4")



16A 250Vac (max fuse rating*) T-55 to T+70 (ambient)
Maximum dissipation wattage: 4W



16A UL 94V2 UL file E92075 CSA file LR44770

RoHS

RoHS compliant

These products comply with safety category PC2.


*Users should be aware of the de-rating factors published by specialist manufacturers of fuses.

Fuseholders with in-line termination have combination (4.8/6.3) terminals. It has not been possible to show both views here. Units with right angle terminals have user specified end terminals and combination mid-body terminals.

- ▶ 6.3 x 32mm fuses
- ▶ Screwdriver slot knob
- ▶ PC2 protection category
- ▶ 4.8, 6.3 and solder terminals
- ▶ Low profile bezel
- ▶ Snap in or threaded bushing mounting options



ORDER FORMAT



M873

Cover for C & T terminals



A0035 00

In-line 6.3 x 32 (1 1/4 x 1/4) fuseholder
Extra low voltage 5A Max

▶ TERMINAL	▶ BODY AND CAP	▶ PANEL HOLE	DIMENSIONS (mm)
C 6.3 x 0.8 9.1	0345 (C terminal shown) Screwdriver release 	RA 2.5 17.3 17.4 16.0/16.1	0345 (C terminal shown) 9.1 42.0 3.0 19.5
D 6.3 x 0.8 Right angle 9.1	0345 (D terminal shown) Screwdriver release 	Panel thickness 0.8 - 2.0mm for snap fit 0.8 - 7.0mm for screw to panel fixing	0345 (D terminal shown) 9.1 39.0 42.0 3.0 19.5
T 4.1 2.8 4.8 x 0.8 Solder 9.1	0347 (T terminal shown) Screwdriver release 	RD 15.0 15.1 16.0/16.1	0347 (C terminal shown) 9.1 42.0 3.0 19.5
U 4.1 2.8 4.8 x 0.8 Right angle solder 9.1	0347 (U terminal shown) Screwdriver release 	Panel thickness 0.8 - 2.0mm for snap fit 0.8 - 7.0mm for screw to panel fixing	0347 (D terminal shown) 9.1 39.0 42.0 3.0 19.5

Optional metal fixing nut available for 0347