

## Cable glands Progress® EMC nickel-plated brass with contact sleeve



### Short entry thread metric

#### Type approval: Progress MS EMV

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1080.63.500</b>
E-No:	121072918
EAN:	7611614119571
Material	Nickel-plated brass
Contact sleeve	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Properties	Excellent shield contact through the contact sleeve with the braided shield terminating in the screwed cable gland
Entry thread	M63x1.5
Clamping range without insert min.	46.0 mm
Clamping range without insert max.	50.0 mm
Wrench size	70 mm
Dimension H	39 mm
Thread length L	10 mm
Dispatch	5

1 = Metric coarse-pitch thread (with VDE test report)

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.