



General Product Information	Insulating material	—
	Inflammability class acc. to UL 94	—
	Packing Unit	—
	Weight (g)	—
TSE / CE Technical Data	Nominal Voltage	600 V ~
	Nominal Current	41 A
	Cross Section	6 mm ²
	Norm	EN 60998-2-1
VDE Technical Data	Nominal Voltage	— V ~
	Nominal Current	— A
	Cross Section	6 mm ²
	VDE Norm	IEC 60998-1/IEC 60998-2-1
UL / CSA Technical Data	Nominal Voltage	— V ~
	Nominal Current	— A
	Cross Section	6
Connection Data	Minimum solid strand cross section	— mm ²
	Maximum solid Strand cross section	— mm ²
	Minimum fine Strand cross section	— mm ²
	Maximum fine strand cross section	— mm ²
	AWG Conductor Range	—
	Connection Type	screw/vidal
	Insulation Stripping length	9 mm
	Tightening torque	0.5/0.8 Nm

Avrupa standartlarına uygunluk belgesi - CE Certificate

Türk Standartlarına Uygunluk Belgesi - TSE Certificate

LAPEM - RETIE Sertifikası - LAPEM - Retie Certificate

Order Info

421020

© 2022 Klemsan A.Ş.
www.klemsan.com