



## NC4FDX-TOP

4 pole female chassis connector, TRUE OUTDOOR PROTECTION (TOP)

The X-TOP series is a "heavy-duty" XLR chassis connector for outdoor use. Outdoor protected by mating with related cable connector of the XLR TOP range (IP65 and UL50E). Gold contacts are standard.

### Features & Benefits

- Heavy-duty sealed XLR connector range for harsh and demanding environment
- High impact UV-resistant materials
- Outdoor protection according to IP65. Maintains sealing when in use and when disconnected
- IEC 61984 certified

## Technical Information

Product	
<b>Title</b>	NC4FDX-TOP
<b>Connection Type</b>	XLR
<b>Gender</b>	Female

Electrical	
<b>Contact resistance</b>	$\leq 5 \text{ m}\Omega$
<b>Dielectric strength</b>	1,5 kVdc
<b>Insulation resistance</b>	$> 10 \text{ G}\Omega$ (initial)
<b>Rated current per contact</b>	10 A
<b>Rated voltage</b>	50 V

Mechanical	
<b>Insertion force</b>	$\leq 20 \text{ N}$
<b>Withdrawal force</b>	$\leq 20 \text{ N}$
<b>Lifetime</b>	$> 1000$ mating cycles
<b>Wiring</b>	Solder contacts
<b>Locking device</b>	Latch lock
<b>Mounting direction</b>	Front mounting
<b>Chassis shape</b>	D

Material	
<b>Contact plating</b>	Gold (Au) over Nickel (Ni)
<b>Contacts</b>	Brass
<b>Insert</b>	Polyamide
<b>Locking element</b>	Stainless steel
<b>Gasket</b>	TPE
<b>Shell</b>	Polyamide

Environmental	
<b>Flammability acc. to UL94</b>	V-0
<b>Standard compliance</b>	IEC 61076-2-103
<b>Protection class acc. IEC 60529</b>	IP65
<b>Solderability acc. to</b>	IEC 60068-2-20
<b>Temperature range</b>	-30 °C to +80 °C
<b>Pollution degree acc. to IEC 60664-1</b>	II