


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PUI AUDIO, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT WRITTEN PERMISSION OF PUI AUDIO, INC. IS PROHIBITED.
© 2010, PUI AUDIO Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RESONANT FREQUENCY	3,400±500	Hz
RESONANT IMPEDANCE (MAX)	1000	Ohm
MAX INPUT VOLTAGE	30	Vp-p
CAPACITANCE @ 1kHz	13,000±30%	pF
PLATE MATERIAL	BRASS	-
OPERATING TEMPERATURE	-20 ~ +60	°C
STORAGE TEMPERATURE	-20 ~ +70	°C


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	3/19/20	

PRELIMINARY



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. CONNECTOR: AMPHENOL 90311-004LF.
TERMINAL: AMPHENOL 77138-101LF.
4. THIS PART IS RoHS 2015/863/EU COMPLIANT WITH EXEMPTION 7c-1.

UNLESS OTHERWISE SPECIFIED: ALL PURCHASES ARE SUBJECT TO THE PUI AUDIO TERMS AND CONDITIONS SALE FOUND AT http://www.puiaudio.com/pdf/terms_conditions.pdf (paper copy available upon request). DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.		 pui audio inc 3541 Stop Eight Road Dayton, OH 45414
APPROVALS	DATE	
DRAWN	M.L.	3/20
CHECKED	M.L.	3/20
APPROVED	B.R.	3/20
DRAWING NO. AB2734B-LWC77-R		SCALE: N.T.S.
SHEET 1 OF 1		

BASE PART:
AB2734B-LW100-R

FILE NAME
AB2734B-LWC77-R.DWG

BENDER

DRAWING NO. AB2734B-LWC77-R

SIZE A

SHEET 1 OF 1